


# 吹氣式濃縮機

## Pressured Gas Blowing Concentrator

### MGS-2200




MGS-2200



MGS-2200 + MGS HEAT

型號	MGS-2200
溫度使用範圍	室溫 +5.0 ~ 200°C
溫度調節精度	± 0.1 ~ 0.2°C
溫度控制方式	PID 空溫，LED 顯示
程控設定模式	Auto Stop, Auto Start, 2 Step
可放置鋁塊數	1 個，90 W × 135 D × 70 H (mm)
MGS-HEAT	室溫 +5 ~ 80°C 加熱氣體



型號	吹氣架		加熱鋁塊			
	型號	管數	型號	試管外徑	孔數	
MGS-2200	A	S-048	48	MGB-0548	8 mm, 0.5 mL	48
	B	S-040	40	MGB-1540	11 mm, 1.5 mL	40
	C			MGB-1240	12 mm	40
	D	S-024	24	MGB-1524	15 mm	24
	E			MGB-1624	16.5 mm	24
	F	S-022	22	MGB-1822	18 mm	22
	G	S-016	16	MGB-2116	21 mm	16
	H	S-012	12	MGB-2412	24 mm	12
	I			MGB-2512	25 mm	12

### MG-1200 (單槽)

### MG-2300 (雙槽)

- 需依尺寸選購加熱鋁塊
- 控制功能同上方 MGS-2200 系型
- 加熱鋁塊數：MG-1200：1 個  
MG-2300：2 個
- 可加裝 Thermal Sensor 做實際溫控
- 控溫精度高達 ± 0.1 ~ 0.2°C
- 可做 Auto start, Auto stop, 2 step program.

### 精密型乾式恆溫反應槽

4 ~ 100°C (冷熱兩用型)

室溫 ~ 200°C (高溫型)



MG-1200

酵素反應及低溫恆溫用



MG-2300

催化及水解反應用

