

Microcentrifuge 5424

全新桌上型超高速離心機

轉子種類



Technical specifications, rotors for Centrifuge 5424

Rotor	Adapter	Max. ref (xg)
		230 V, 14,680 rpm
FA - 45 - 24 - 11, FA - 45 - 24 - 11 - Special	Without Adapter	20,238 × g
	0.2 ml	15,179 × g
	0.4 ml	20,238 × g
	0.5 ml	17,588 × g
	0.6 ml	20,238 × g
F - 45 - 18 - 11 - Kit	Without Adapter	17,347 × g
	0.2 ml	12,288 × g
	0.4 ml	17,347 × g
	0.5 ml	14,697 × g
	0.6 ml	17,347 × g
F - 45 - 32 - 5 - PCR		17,829 × g

● The Kit rotor with the extended rim for safe centrifugation of spin columns with open tube lids.

i Adapter for rotors see page 117.

Ordering information

Description	Order no.
Rotor FA - 45 - 24 - 11 , incl, rotor lid, aerosol - tight	5424 702.007
Rotor lid for FA - 45 - 24 - 11, aerosol - tight	5424 703.003
Rotor FA - 45 - 24 - 11 - Special , incl, rotor lid, aerosol - tight, coated	5424 700.004
Rotor lid for FA - 45 - 24 - 11 - Special, aerosol - tight, coated	5424 701.000
Rotor F - 45 - 18 - 11 - Kit , incl, rotor lid	5424 706.002
Rotor lid for F - 45 - 18 - 11 - Kit	5424 707.009
Rotor F - 45 - 32 - 5 - PCR , incl rotor lid	5424 704.000
Rotor lid for F - 45 - 32 - 5 - PCR	5424 708.005
Rotor key (see 5417 C / R, 5702 / 5702 R / 5702 RH)	5416 301.001